


HiFLOW

In-Line Mains Water Filter System

Specifications



Parts Supplied

- 1 WFA QL-2 Filter Head Assembly
- 2 WFA Hi Flow Filter Cartridge
- 3 Mounting Screws (4 off)
- 4 Dual Check Valve
- 5 Pex Hose 550mm
- 6 Brass Nipple 3/8" NPTF to 1/2" m BSP
- 7 Horizontal Stabilising Bracket
- 8 Filter Monitor Alarm
- 9 Plumbing Tape

Performance

The WFA HiFlow Filter removes/reduces:

- Chlorine
- Tastes & Odours
- Cryptosporidium
- Giardia
- Lead
- Mould & Algae
- Sulphides Oxidised
- Rust
- Limescale
- Dirt & Other Particles down to 0.5 microns in size
- Oxidised Iron



Water
Filters
AUSTRALIA



HiFLOW

Model No.
WFAHiFlow

Specifications

Specifications

	Vertical	Horizontal
Height	51cm	13cm
Width	13cm	51cm
Depth	13cm	13cm
Capacity	11,355 litres	
Pressure	70 - 860 kPa (10 - 125 psi)	
Temperature	2 - 38° C (35 - 100° F)	
Flow Rate	8.3 litres per minute	

Requirements

Inlet Connection: ½" BSP Male
 Install vertically with cartridge hanging down or horizontally with stabilising bracket installed
 Flush new cartridge at full flow for 2 to 3 minutes to purge air.

Cartridges require replacement when;

- Capacity is reached
- Flow becomes too slow
- Every 12 months.

Whichever occurs first.
 No electrical connections required.

Schedule of Works

Suggested mounting location diagrams:

Installer

- Locate ½ inch male BSP connection to cold water supply in cupboard underneath kitchen sink.
- Install the components of the WFA HiFlow water filtration system under kitchen sink in accordance with the installation instructions supplied.
- Ensure that all plumbing work carried out in the installation of the system complies with Australian Standard AS3500.
- When installed purge air from system for 2-3 minutes.
- Fix any leaks if present.
- Complete warranty card online at www.waterfiltersaust.com.au or mail to WFA
- Activate Cartridge Monitor Alarm



HiFlow
In-Line Mains Water Filter System

Special Notices

- Installation instructions and standard warranty are included with the WFA HiFlow In-Line Water Filter System when shipped.
- The WFA HiFlow In-Line Water Filter System must be maintained according to manufacturer's instructions, including replacement of filter cartridges.
- Do not use the WFA HiFlow In-Line Water Filter System with water that is microbiologically unsafe, or of unknown quality without adequate disinfection before or after the system; the WFA HiFlow In-Line Water Filter System is certified for cyst reduction and may be used on disinfected waters that may contain filterable cysts.
- The contaminants or other substances removed by this water treatment system are not necessarily in your water
- Check for compliance with state and local laws and regulations



Water Filters Australia Pty Limited ABN: 78089 574 489
 Unit 11, 26 Wattle Road BROOKVALE NSW 2100 Australia
 PO Box 636 FRESHWATER NSW 2096 Australia

T +61 2 9905 6211 F +61 2 9905 6255
 E info@hiflowfilter.com.au W www.hiflowfilter.com.au

HiFlow
 Model No.
 WFAHiFlow